

HSP-1 & HSP-1-P Pot Heat Sealers

POT HEAT SEALERS FOR LAB SCALE / PROTOTYPE PRODUCTION OF REPEATABLE HIGH QUALITY HEAT SEALS IN POT / LIDDING FILM APPLICATIONS. CUSTOMISABLE TO PRODUCE SEALS TYPICALLY UP TO 150MM DIAMETER.



The HSP-1 and HSP-1-P Pot Heat Sealers are a customisable technology to deliver high quality heat seals for pot/lidding film packaging. A custom made pot holder and sealing platen are specified for individual sealed packs, or multiple seals across a pack.

Pot loading is done manually, and the lidding film is either drawn off a small roll or placed manually. Panel controls give flexible setting of sealing parameters (temperature, pressure, dwell time), and alerts users to out of tolerance settings, or errors in the sealing sequence.

The robust frame, with 'pack-in-place' sensors, easy to use controls, and interlocked sliding guards ensure safe and repeatable operation, time after time.

TESTING SOLUTIONS



RDM Test Equipment Unit 39 Golds Nurseries Bus. Park Jenkins Drive, ELSENHAM Hertfordshire, CM22 6JX, UK

nqa


ISO 9001

Tel: +44(0)1279 817171 Fax: +44(0)1279 815743 E-mail: sales@rdmtest.com Web: www.rdmtest.com

HSP-1 & HSP-1-P Pot Heat Sealers



FOR PRODUCTION OF HIGH QUALITY HEAT SEALS FOR LIDDING FILMS ON POTS, CONTAINERS, PODS AND BLISTER PACKS



Benefits:

- Highly customisable technology to suit the application with heat sealing jaw configuration
- Validate to ISO11607, or internal standards
- High quality repeatable seals, not influenced by operator
- Versatile applications for pots, containers, blister packs and trays, custom designs as required
- Low Maintenance 12 months between calibrations

Features:

- Precise control of temperature, pressure and dwell time.
- Precise pressure calibration of standard surface area jaw face
- Jaws constructed in aluminium with precision ground faces
- Range of jaw face surfaces including Flat Metal, and Teflon Coating

Models:

- **HSP-1:** Flat sealing head 150 x 150mm (fixed) with customised pot holder (interchangeable). Heat Sealer control module with digital temperature, dial pressure gauge and analogue dwell timer (as per HSM-4)
- **HSP-1-P:** Profile sealing head up to 150 x 150mm (interchangeable) with customised pot holder (interchangeable). Heat Sealer control module with digital temperature, dial pressure gauge and analogue dwell timer (as per HSM-4)



ASSURED QUALITY TESTING SOLUTIONS





RDM Test Equipment Unit 39 Golds Nurseries Bus. Park Jenkins Drive, ELSENHAM Hertfordshire, CM22 6JX, UK

> Tel: +44(0)1279 817171 Fax: +44(0)1279 815743 E-mail: sales@rdmtest.com Web: www.rdmtest.com